

SmartTEMP S

38

Portable induction heater.
Combines all the features of the SmartTEMP range in a compact device.
Lightweight and easy to use, can heat a part weighing up to **50 kg**.



BENEFITS

- Small, **light** heater: weighs only 21 kg. 230 V/13 A power supply.
- **High performance**: Designed for all bearings and rotating parts with a bore diameter above **10 mm** with a maximum diameter of **400 mm** and a maximum weight of **50 kg**.
- **Safe**: 4 heating modes: Time, Ramp, Temperature (1 sensor), Temperature (2 sensors). Second sensor optional.
- **Easy to use**: Interactive touch screen enabling precise control of the device (heating settings and graphics). Several languages available.
- **Extraction** of heating data (USB).

Delivered as standard with its 3 yokes, a pair of gloves and a sensor. (Optional carrying case)

COMMERCIAL REFERENCE

TOOL SMART TEMP S / induction heater

SmartTEMP M

38

Induction heater with pivoting yoke, a best-seller for maintenance or production workshops, which can heat a bearing weighing up to **100 kg**.



BENEFIT

- Used as fixed equipment. 230 V/16 A power supply.
- It is **compact**, weighing only 40 kg, and can be easily moved using its 2 side handles.
- **High performance**: Designed for all bearings and rotating parts with a bore diameter above **10 mm** with a maximum diameter of **500 mm** and a maximum weight of **100 kg**.
- **Safe**: 4 heating modes: Time, Ramp, Temperature (1 sensor), Temperature (2 sensors). Second sensor optional.
- **Easy to use**: Interactive touch screen enabling precise control of the device (heating settings and graphics). Several languages available.
- **Extraction** of heating data (USB).
- **Ergonomic** with its standard pivoting yoke which facilitates the loading of the parts to be heated.

Delivered as standard with a probe, a pair of gloves and a yoke for bore diameter greater than or equal to 70 mm. Other yoke sizes are available as an option and must be ordered according to the application.

COMMERCIAL REFERENCE

TOOL SMART TEMP M / induction heater