

ADJUSTABLE SPANNERS

Reference	TOOL PS (size) / Pin spanner	
Description	Articulated manual pin spanner	
Material	Hardened, forged chrome vanadium steel. Satin chrome finish	
Pin hardness	40 HRC	
Use	Tommy nuts (examples of accuracy: TB, TBR, TBP, TBPR, etc.)	
References	Nut diameter (mm)	Pin diameter (mm)
TOOL PS 15-35	15-35	3
TOOL PS 35-50	35-50	4
TOOL PS 50-80	50-80	5
TOOL PS 80-120	80-120	6
TOOL PS 120-180	120-180	8

References	TOOL HS (size) / Hook spanner	
Description	Articulated manual hook spanner	
Material	Hardened, forged chrome vanadium steel. Satin chrome finish	
Use	Slot nuts (e.g.: KM, KML, ..., B, BR, BP, ...)	
References	Nut diameter (mm)	
TOOL HS 15-35	15-35	
TOOL HS 35-50	35-50	
TOOL HS 50-80	50-80	
TOOL HS 80-120	80-120	
TOOL HS 120-180	120-180	