

## SELF-CENTERING HYDRAULIC PULLER (combined with 2 or 3 arms)

Reference	TOOL SCHP (Capacity) TONS / Self-Center Hyd Puller											
Type	Capacity (ton)	Max. gripping distance (mm)	Cylinder stroke H (mm)	Spread (mm)		Dimensions (mm)						Weight (kg)
				Min.	Max.	A	B	C	E	F	G	
SCHP 4 Tons	4	190	60	68	315	13	10	22	40	42	22	9
SCHP 12 Tons	12	300	85	90	463	15	16.5	29	70	60	28	17
SCHP 20 Tons	20	325	111	120	520	20	27	33	62	80	40	28
SCHP 30 Tons	30	415	111	120	620	20	27	38	85	98	50	39

